

Eaton V48D28T2216

Catalog Number: V48D28T2216

Eaton General purpose ventilated transformer, DOE 2016 Efficient, NEMA 2, 60 Hz, 220°C, 225 kVA, Three-phase, 480 Delta V, 208Y/120 Vac, NEMA ST-20, +2 at 2.5%, -2 at 2.5%, 150°C, Aluminum windings



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48D28T2216
	UPC
	786680232930
Product Length/Depth	Product Height
33.5 in	60 in
Product Width	Product Weight
38 in	1615 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
10 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR944

Insulation

220 °C

Mounting

Floor

Tap size

+2 at 2.5%, -2 at 2.5%

Type

Energy-efficient ventilated type DT-3 transformer

Wiring connection

266W

Miscellaneous

Weathershield

WS61

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

225 kVA

Voltage rating

480 Vac-208Y/120 Vac

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48D28T2216](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)