

Eaton V48D28T2216CUESLS52

Catalog Number: V48D28T2216CUESLS52

Eaton General purpose ventilated transformer, Copper windings, NEMA 2, 60 Hz, 220°C, 225 kVA, Floor, Three-phase, 480 Delta V, 208Y/120 Vac, Low sound 52 dB, +2 at 2.5%, -2 at 2.5%, 150°C, 225 kVA, 480 Vac-208Y/120 Vac, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48D28T2216CUESLS52
	UPC
	786680204456
Product Length/Depth	Product Height
33.5 in	60 in
Product Width	Product Weight
38 in	1.1 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor

Tap size

+2 at 2.5%, -2 at 2.5%

Type

Energy-efficient ventilated type DT-3 transformer

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

52 dB

Temperature rise

150 °C rise

Volt ampere rating

225 kVA

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Modification 1

Electrostatic shield

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48D28T2216CUESLS52](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)