

Eaton V48M22T4516LS42

Catalog Number: V48M22T4516LS42

Eaton General purpose ventilated transformer, Fungus proof, AL wndng, DOE2016, NEMA 2, FR940, 45 kVA, FI/wall mt upright, 3-ph, PV: 480V dlt, SV: 240V dlt w/120V midtap, 42 dB, 2 at +2.5%, 4 at -2.5%, 45 kVA, WS58, 282B



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M22T4516LS42
	UPC
	786680219689
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	426 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR940

Insulation

220 °C

Material

Al windings

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

282B

Miscellaneous

Weathershield

WS58

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

45 kVA

Primary voltage

480 V delta

Secondary Voltage

240 V delta, 120 V Midtap

Sound Level

42 dB

Temperature rise

150 °C rise

Volt ampere rating

45 kVA

Voltage rating

480 Vac-240 Vac/120 Vac

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M22T4516LS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)