

Eaton V48M22T5016

Catalog Number: V48M22T5016

50 kVA DOE 2016 Ventd XFMR 3PH 480-240 DELTA 120V
LIGHTING TAP (PH B), 150 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M22T5016
	UPC
	786680231049
Product Length/Depth	Product Height
24 in	43 in
Product Width	Product Weight
30.5 in	597 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
17 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR942

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

282B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

50 kVA

Primary voltage

480 V

Secondary Voltage

240 V, 120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

50 kVA

Miscellaneous

Weathershield

942

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M22T5016](#)