

Eaton V48M28B4516CULS45

Catalog Number: V48M28B4516CULS45

Eaton General purpose ventilated transformer 45 kVA DOE 2016
Ventd XFMR 3PH 480-208Y/120, 80 °C rise, Copper,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28B4516CULS45
	UPC
	786680230981
Product Length/Depth	Product Height
24 in	43 in
Product Width	Product Weight
30.5 in	667 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
33 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR942

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

280B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

45 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

45 dB

Temperature rise

80 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Weathershield

942

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28B4516CULS45](#)