

Eaton V48M28B4916S6TR

Catalog Number: V48M28B4916S6TR

Eaton Eaton General purpose ventilated transformer, Fungus proof, AL wndng, DOE2016, Grade 316-SS, 220°C, 150 kVA, Cert prod test report, Fl/wall mt upright, 3-ph, PV 480V dlt, SV 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 80°C



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28B4916S6TR
	UPC
	786680205170
Product Length/Depth	Product Height
33.5 in	60 in
Product Width	Product Weight
38 in	1.1 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Type

Energy-efficient ventilated dry-type transformer

Performance Ratings

Sound Level

NEMA ST-20

Voltage rating

480 Vac-208Y/120 Vac

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28B4916S6TR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)