

Eaton V48M28E7516LS47

Catalog Number: V48M28E7516LS47

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, 220°C, 75 kVA, E-S shield, Floor/wall mnt upright only, 3-phase, PV: 480V delta, SV: 208Y/120, 47 dB, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

V48M28E7516LS47

UPC

786680178450

Product Length/Depth

24 in

Product Height

43 in

Product Width

30.5 in

Product Weight

450 lb

Warranty

Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

283B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

75 kVA

Primary voltage

480 V delta

Secondary Voltage

208Y/120 V

Sound Level

47 dB

Temperature rise

150 °C rise

Volt ampere rating

75 kVA

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Modification 1

Electrostatic shield

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28E7516LS47](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)