

Eaton V48M28F4916CUESLS47

Catalog Number: V48M28F4916CUESLS47

Eaton General purpose ventilated transformer, Fungus proof, CU windings, DOE 2016, NEMA 2, 220°C, 150 kVA, E-S shield, Floor/wall mnt upright only, 3-phase, PV: 480V delta, SV: 208Y/120, 47 dB, 2 at +2.5%, 4 at -2.5%, 115°C, 150 kVA



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

V48M28F4916CUESLS47

UPC

786680205224

Product Length/Depth

31.5 in

Product Height

51 in

Product Width

34.5 in

Product Weight

1432 lb

Warranty

Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

283B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

150 kVA

Primary voltage

480 V delta

Secondary Voltage

208Y/120 V

Sound Level

47 dB

Temperature rise

115 °C rise

Volt ampere rating

150 kVA

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Modification 1

Electrostatic shield

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28F4916CUESLS47](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)