

Eaton V48M28F4916CULS45

Catalog Number: V48M28F4916CULS45

Eaton DOE 2016 Efficient Transformer, 150 kVA, Ventd XFMR
3PH 480-208Y/120, 115C rise, Copper windings, 45dB Sound



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28F4916CULS45
	UPC
	786680226960
Product Length/Depth	Product Height
31.5 in	51 in
Product Width	Product Weight
34.5 in	1390 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

943

Insulation

220 °C

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Wiring connection

280B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

150 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

45 dB

Temperature rise

115 °C rise

Volt ampere rating

150 kVA

Miscellaneous

Weathershield

WS60

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28F4916CULS45](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)