

Eaton V48M28T12CUNV

Catalog Number: V48M28T12CUNV

General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 112.5 kVA, Cu windings, Frame: 917



Photo is representative

General specifications

Product Name

Eaton Totally enclosed non-ventilated transformer

Catalog Number

V48M28T12CUNV

UPC

786685198002

Product Length/Depth

24.67 in

Product Height

32.02 in

Product Width

31.44 in

Product Weight

1431 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Totally enclosed non-ventilated



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

DT-3

Frame

917

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

112.5 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T12CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)