

Eaton V48M28T1516SS

Catalog Number: V48M28T1516SS

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, Grade 304-SS, FR939, 15 kVA, FI/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 15 kVA, WS57, 280B



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

V48M28T1516SS

UPC

786680221019

Product Length/Depth

17.75 in

Product Height

28 in

Product Width

21.88 in

Product Weight

241 lb

Warranty

Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR939

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

280B

Miscellaneous

Modification 1

Grade 304 stainless steel enclosure (does not imply a NEMA 4X rating)

Weathershield

WS57

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

480 V delta

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Voltage rating

480 Vac-208Y/120 Vac

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T1516SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)