

Eaton V48M28T1516TRLS42

Catalog Number: V48M28T1516TRLS42

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, 220°C, 15 kVA, Cert prod test report, Floor/wall mnt upright only, 3-ph, PV: 480V delta, SV: 208Y/120, 42 dB, 2 at +2.5%, 4 at -2.5%, 150°C, 15 kVA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28T1516TRLS42
	UPC
	786680205750
Product Length/Depth	Product Height
17.75 in	28 in
Product Width	Product Weight
21.88 in	224 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

280B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

480 V delta

Secondary Voltage

208Y/120 V

Sound Level

42 dB

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Modification 1

Certified test report of standard production tests for the specific serial number to be shipped

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T1516TRLS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)