

Eaton V48M28T2216CUESLS52

Catalog Number: V48M28T2216CUESLS52

225 kVA DOE 2016 Ventd XFMR 3PH 480-208Y/120, 150 °C rise, Copper, Shielded



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28T2216CUESLS52
	UPC
	786680230929
Product Length/Depth	Product Height
33.5 in	60 in
Product Width	Product Weight
38 in	1915 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
30 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR944

Insulation

220 °C

Mounting

Floor

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

283B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

52 dB

Temperature rise

150 °C rise

Volt ampere rating

225 kVA

Miscellaneous

Modification 1

Shielded

Weathershield

944

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T2216CUESLS52](#)