

Eaton V48M39T3316

Catalog Number: V48M39T3316

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, 300 kVA, Floor mnt, 3-phase, PV: 480V delta, SV: 400V, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 300 kVA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M39T3316
	UPC
	786680196904
Product Length/Depth	Product Height
33.5 in	66.18 in
Product Width	Product Weight
42.18 in	2315 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

281B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

300 kVA

Primary voltage

480 V delta

Secondary Voltage

400 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

300 kVA

Voltage rating

480 Vac-400 Vac

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M39T3316](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)