

Eaton V48M47B2216

Catalog Number: V48M47B2216

Eaton General purpose ventilated transformer, 225 kVA DOE 2016 Ventd XFMR 3PH 480-480Y/277, 80 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M47B2216
	UPC
	786680230172
Product Length/Depth	Product Height
33.5 in	66.18 in
Product Width	Product Weight
42.18 in	2218 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
45 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR945

Insulation

220 °C

Mounting

Floor

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

280B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Sound Level

NEMA ST-20

Temperature rise

80 °C rise

Volt ampere rating

225 kVA

Miscellaneous

Weathershield

945

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M47B2216](#)