

Eaton V48M47B3016

Catalog Number: V48M47B3016

Eaton General purpose ventilated transformer, 30 kVA DOE 2016
Ventd XFMR 3PH 480-480Y/277, 80 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M47B3016
	UPC
	786680230714
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	444 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
142 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR940

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

280B

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Sound Level

NEMA ST-20

Temperature rise

80 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

940

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M47B3016](#)