

Eaton V48M64T4916

Catalog Number: V48M64T4916

150 kVA DOE 2016 Ventd XFMR 3PH 480-240Y/139, 150 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M64T4916
	UPC
	786680230769
Product Length/Depth	Product Height
31.5 in	51 in
Product Width	Product Weight
34.5 in	1270 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
23 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR943

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

280B

Miscellaneous

Weathershield

943

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

150 kVA

Primary voltage

480 V

Secondary Voltage

240Y/139 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

150 kVA

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M64T4916](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)