

Eaton V50N34T42XCE

Catalog Number: V50N34T42XCE

Eaton General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 380/400/415/440/480V, Taps: None, SV: 400Y/231V, 150°C, 415 kVA, Al windings , Frame: 920, uses WS35, CE marked



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V50N34T42XCE
	UPC
	786680091933
Product Length/Depth	Product Height
36.23 in	75 in
Product Width	Product Weight
44.2 in	2991 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	CE Marked

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

920

Tap size

None

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

50-60 Hz

Kva Rating

415 kVA

Primary voltage

380 V, 400 V, 415 V, 440 V, 480 V

Secondary Voltage

400Y/231 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS35

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V50N34T42XCE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)