

Eaton V55M47F3016CUESLS40

Catalog Number: V55M47F3016CUESLS40

30 kVA DOE 2016 Ventd XFMR 3PH 550-480Y/277, 115 °C rise,
Copper, Shielded



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V55M47F3016CUESLS40
	UPC
	786680230554
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	455 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
78 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR940

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

283S

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

550 V

Secondary Voltage

480Y/277 V

Sound Level

40 dB

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Modification 1

Shielded

Weathershield

940

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V55M47F3016CUESLS40](#)