

# Eaton WP832

Catalog Number: WP832

Eaton Crouse-Hinds series WP plug, 20A, Two-wire, three-pole, Copper-free aluminum, 5-20P, 0.500-0.625" cord diameter, 125 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series WP plug	WP832
UPC	Product Length/Depth
782274085333	3.5 in
Product Height	Product Width
2.5 in	2.5 in
Product Weight	
0.3 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Material

Copper-free aluminum

### Amperage Rating

20A

### Voltage rating

125 Vac

### NEMA configuration

5-20P

### Special features

0.500-0.625" cord diameter

## Resources

### Catalogs

[Crouse-Hinds series FS, FD, Single, Multi, Blank Device Boxes and Covers catalog page](#)

### Certification reports

[FS and FD Device Boxes and Covers Canadian CSA certification](#)

[FS and FD Device Boxes and Covers UL certification](#)

[FS and FD Device Boxes and Covers Canadian certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - WP832](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)