

Eaton WSQC5640

Catalog Number: WSQC5640

Eaton Crouse-Hinds series Arktite WSQC interlocked receptacle with enclosed switch, 60A, Three-wire, four-pole, Brass contacts, Copper-free aluminum, 1-1/2", 120-600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite WSQC interlocked receptacle with enclosed switch	WSQC5640 UPC 782274018065
Product Length/Depth	Product Height
5 in	14.44 in
Product Width	Product Weight
7 in	13.99 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

12

Product specifications

Enclosure type

With switch

Amperage Rating

60A

Trade size

1-1/2"

Configuration

Three-wire, four-pole

Voltage rating

120-600 Vac

Material

Copper-free aluminum

Contact material

Brass

Resources

Catalogs

[Arktite WSQC Interlock Receptacles catalog page](#)

Certification reports

[Arktite WSQC Interlock Receptacles Canadian certification](#)

[Arktite WSQC Interlock Receptacles UL certification](#)

Installation instructions

[IF 1371 - WSQ Series 30 and 60A Interlock Receptacle](#)

Specifications and datasheets

[Eaton Specification Sheet - WSQC5640](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)