

Eaton WSR103542

Catalog Number: WSR103542

Eaton Crouse-Hinds series Arktite WSR interlocked receptacle with enclosed disconnect switch, 100A, 3-wire, 4-pole, Brass contacts, Solid door, Non-fused, Style 2, 30 HP/60 HP/75 HP, Copper-free alum, Spring door, 1-1/2", 240-600 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite WSR interlocked receptacle with enclosed disconnect switch	WSR103542
	UPC
	782274019529
Product Length/Depth	Product Height
14.88 in	35.38 in
Product Width	Product Weight
8.25 in	61 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

4

12

Product specifications

Door style

Solid

Amperage Rating

100A

Fusing

Non-fused

Grounding style

Style 2

Configuration

Three-wire, four-pole

Material

Copper-free aluminum

Contact material

Brass

Voltage rating

240-600 Vac

Horsepower

30 hp/60 hp/75 hp

Receptacle style

Spring door

Trade size

1-1/2"

Resources

Catalogs

[Arktite WSR/WSRD Interlock Receptacles catalog page](#)

Certification reports

[Arktite WSR/WSRD Interlock Receptacles with Enclosed Disconnect Switches UL certification](#)

[Arktite WSR/WSRD Interlock Receptacles with Enclosed Disconnect Switches Canadian certification](#)

Installation instructions

[IF 1315 - WSR Series Model 94 Interlock Receptacle](#)

[IF 943 - WSR Series Model 82 Interlock Receptacle](#)

Specifications and datasheets

Eaton Specification Sheet - WSR103542



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)