

# Eaton WSR3352

Catalog Number: WSR3352

Eaton Crouse-Hinds series Arktite WSR interlocked receptacle with enclosed disconnect switch, 30A, Three-wire, four-pole, Brass contacts, Solid door, Fused, Style 2, 7.5 HP/15 HP/20 HP, Copper-free aluminum, Spring door, 1", 240-600 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite WSR interlocked receptacle with enclosed disconnect switch	WSR3352
	UPC
	782274019420
Product Length/Depth	Product Height
11.75 in	27.69 in
Product Width	Product Weight
7.25 in	36 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

4

12

## Product specifications

### Door style

Solid

### Amperage Rating

30A

### Fusing

Fused

### Grounding style

Style 2

### Configuration

Three-wire, four-pole

### Material

Copper-free aluminum

### Contact material

Brass

### Voltage rating

240-600 Vac

### Horsepower

7.5 hp/15 hp/20 hp

### Receptacle style

Spring door

### Trade size

1"

## Resources

### Catalogs

[Arktite WSR/WSRD Interlock Receptacles catalog page](#)

### Certification reports

[Arktite WSR/WSRD Interlock Receptacles with Enclosed Disconnect Switches UL certification](#)

[Arktite WSR/WSRD Interlock Receptacles with Enclosed Disconnect Switches Canadian certification](#)

### Installation instructions

[IF 943 - WSR Series Model 82 Interlock Receptacle](#)

[IF 1315 - WSR Series Model 94 Interlock Receptacle](#)

Specifications and datasheets

Eaton Specification Sheet - WSR3352

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)