

Eaton X48M28F7516NON

Catalog Number: X48M28F7516NON

75 kVA DOE 2016 Harm Mtg Ventd XFMR 3PH 480-208Y/120, 115 °C rise, Aluminum, Shielded



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	X48M28F7516NON
	UPC
	786680230301
Product Length/Depth	Product Height
24 in	43 in
Product Width	Product Weight
30.5 in	609 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
55 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR942

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

200X

Miscellaneous

Weathershield

942

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

75 kVA

Phase shift

0 °

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

75 kVA

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - X48M28F7516NON](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)