

Eaton X48M28T1516CUTHR

Catalog Number: X48M28T1516CUTHR

15 kVA DOE 2016 Ventd Harm Mtg XFMR 3PH 480Y-208Y/120,
150 °C rise, Copper, Shielded



Photo is representative

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose ventilated transformer | X48M28T1516CUTHR |
| | UPC |
| | 786680230974 |
| Product Length/Depth | Product Height |
| 17.75 in | 28 in |
| Product Width | Product Weight |
| 21.88 in | 238 lb |
| Compliances | Certifications |
| DOE2016 Efficient | UL Listed |
| Catalog Notes | |
| 93 CFR Part 431 (2016) Efficient | |

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR939

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

B48MD28

Miscellaneous

Weathershield

939

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

15 kVA

Phase shift

30 °

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - X48M28T1516CUTHR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)