

Eaton X48M28T3016CUNONLS42

Catalog Number: X48M28T3016CUNONLS42

30 kVA DOE 2016 Ventd Harm Mtg XFMR 3PH 480-208Y/120, 150 °C rise, Copper, Shielded



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	X48M28T3016CUNONLS42
	UPC
	786680230103
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	474 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
42 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR940

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

200X

Miscellaneous

Weathershield

940

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Phase shift

0 °

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

42 dB

Temperature rise

150 °C rise

Volt ampere rating

30 kVA

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - X48M28T3016CUNONLS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)