

Eaton X48M47F4516CUPOS

Catalog Number: X48M47F4516CUPOS

Eaton Harmonic mitigating transformer, CU windings, DOE 2016, NEMA 2, 45 kVA, Floor mnt, 3-phase, 15° phase shift, PV: 480V delta, SV: 480Y/277, 4-wire, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 115°C, 45 kVA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Harmonic mitigating transformer	X48M47F4516CUPOS
UPC	Product Length/Depth
786680196607	22 in
Product Height	Product Width
39.18 in	29 in
Product Weight	Warranty
651 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
DOE2016 Efficient	Contact Manufacturer UL Listed
Catalog Notes	
10 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Insulation

220 °C

Material

Copper

Mounting

Floor

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient harmonic mitigating transformer

Wiring connection

200X

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

45 kVA

Phase

Three-phase

Phase shift

15 °

Primary voltage

480 V delta

Secondary Voltage

480 V/277 V, four-wire

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

45 kVA

Voltage rating

480-480Y/277V

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - X48M47F4516CUPOS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)