

Eaton XC B2 N0

Catalog Number: XC B2 N0

Eaton Crouse-Hinds series XC electric heater, 6,146 BTU/hr, 1.8 kW, Steel, 15A max., Group B rated, Without built-in room thermostat, 208 Vac

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series XC electric heater	XC B2 N0
	UPC
	662276334304
Product Length/Depth	Product Height
31.34 in	20.3 in
Product Width	Product Weight
8.11 in	61.3 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

NEMA Rating

7

Product specifications

Type

Without built-in room thermostat

Power output

1.8 kW

Heat output

6,146 BTU/hr

Voltage rating

208 Vac

Maximum total amperage

15 A

Material

Steel

Special features

Group B rated

Resources

Catalogs

[XC Series Explosionproof Electric Heaters catalog page](#)

Certification reports

[XC Explosionproof Electric Heaters UL certification](#)

Installation instructions

[IF 1729 - XC Series Explosionproof Electric Heaters](#)

Specifications and datasheets

[Eaton Specification Sheet - XC B2 N0](#)