

Eaton XC B3 N0

Catalog Number: XC B3 N0

Eaton Crouse-Hinds series XC electric heater, 6,146 BTU/hr, 1.8 kW, Steel, 15A max., Group B rated, Without built-in room thermostat, 240 Vac

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series XC electric heater | XC B3 N0 |
| | UPC |
| | 662276008472 |
| Product Length/Depth | Product Height |
| 31.34 in | 20.3 in |
| Product Width | Product Weight |
| 8.11 in | 61.3 lb |

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

NEMA Rating

7

Product specifications

Type

Without built-in room thermostat

Power output

1.8 kW

Heat output

6,146 BTU/hr

Voltage rating

240Vac

Maximum total amperage

15 A

Material

Steel

Special features

Group B rated

Resources

Catalogs

[XC Series Explosionproof Electric Heaters catalog page](#)

Certification reports

[XC Explosionproof Electric Heaters UL certification](#)

Installation instructions

[IF 1729 - XC Series Explosionproof Electric Heaters](#)

Specifications and datasheets

[Eaton Specification Sheet - XC B3 N0](#)