

Eaton XC C2 B2

Catalog Number: XC C2 B2

Eaton Crouse-Hinds series XC electric heater, 12292 BTU/hr, 3.6 kW, Steel, 20A max., With built-in room thermostat, 208 Vac

General specifications




Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series XC electric heater	XC C2 B2
	UPC
	662276334212
Product Length/Depth	Product Height
37 in	20.3 in
Product Width	Product Weight
8.11 in	61.3 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

NEMA Rating

7

Product specifications

Type

With built-in room thermostat

Power output

3.6 kW

Heat output

12292 BTU/Hr

Voltage rating

208 Vac

Maximum total amperage

20 A

Material

Steel

Resources

Catalogs

[XC Series Explosionproof Electric Heaters catalog page](#)

Certification reports

[XC Explosionproof Electric Heaters UL certification](#)

Installation instructions

[IF 1729 - XC Series Explosionproof Electric Heaters](#)

Specifications and datasheets

[Eaton Specification Sheet - XC C2 B2](#)