

# Eaton XTAE007B10T004

Catalog Number: XTAE007B10T004

Eaton XT IEC electronic motor starter, Full voltage non-reversing IEC starter, 7 A, 24 V 50/60 Hz, 1NO, B frame, 45 mm, 2.4-4 A, Screw terminals



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC electronic motor starter	XTAE007B10T004
<b>UPC</b>	<b>Product Length/Depth</b>
782116834358	4.61 in
<b>Product Height</b>	<b>Product Width</b>
4.64 in	1.8 in
<b>Product Weight</b>	<b>Warranty</b>
2.35 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
RoHS Compliant	IEC 60947
ATEX Compliant	CSA Certified
	EN 60947

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

**Amperage Rating**

7A

**Overload range**

2.4-4 A

**Type**

Full voltage non-reversing IEC starter

**Frame size**

45 mm

**Terminals**

Screw terminals

**Coil**

24 Vac, 50/60 Hz

**Contact configuration**

1 NO

**Frame**

B

**Catalogs**[Eaton's Volume 5—Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTAE007B10T004](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)