

Eaton XTFR032DDT

Catalog Number: XTFR032DDT

Eaton XT IEC motor control UL 508 Type F - XT IEC FVR Combination Motor Controller, 32 A, 24V 50/60 Hz, 1NO-1NC auxiliary contact, Frame D, 55 mm, 16 to 63 A, Built in heater, Magnetic trip elements, Type 2 Coordination, Frame Size D, 55 mm, 40 to 65



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC motor control	XTFR032DDT
UPC	Product Length/Depth
786685164809	8.75 in
Product Height	Product Width
6.75 in	15 in
Product Weight	Compliances
8.5 lb	CE Marked
Certifications	
IEC 60947-4-1	
UL Listed file E245398	

defaultTaxonomyAttributeLabel

Amperage Rating

32A

Overload range

16 to 63 A

Type

Type 2 Coordination

Frame size

55 mm

Coil

24 Vac, 50/60 Hz

Contact rating

1 NO, 1 NC auxiliary contact

Frame

D

Special features

Built in heater

Trip type

Magnetic trip elements

Resources

Catalogs

[Motor Control and Protection](#)

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTFR032DDT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)