

Eaton XTFR040DDBD

Catalog Number: XTFR040DDBD

Eaton XT IEC motor control UL 508 Type F - XT IEC FVR Combination Motor Controller, 40 A, 220 Vdc, 1NO-1NC auxiliary contact, Frame D, 55 mm, 16 to 63 A, Built in heater, Magnetic trip elements, Type 2 Coordination, Frame Size D, 55 mm, 40 to 65 A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC motor control	XTFR040DDBD
UPC	Product Length/Depth
786685164885	8.75 in
Product Height	Product Width
6.75 in	15 in
Product Weight	Compliances
8.5 lb	CE Marked

Certifications

UL Listed file E245398
IEC 60947-4-1

defaultTaxonomyAttributeLabel

Amperage Rating

40A

Overload range

16 to 63 A

Type

Type 2 Coordination

Frame size

55 mm

Coil

220 Vdc

Contact rating

1 NO, 1 NC auxiliary contact

Frame

D

Special features

Built in heater

Trip type

Magnetic trip elements

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

[Motor Control and Protection](#)

Drawings

[XTFR_DD 2D Drawing Xchange](#)

[XTFR_DD 3D Inventor](#)

[XTFR_DD AutoCAD 2D Footprint](#)

[XTFR_DD 3D Model Xchange](#)

[XTFR_DD AutoCAD 2D Footprint \(mm\)](#)

[XTFR_DD 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - XTFR040DDBD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)