

Eaton XTMR6A21P

Catalog Number: XTMR6A21P

Eaton XT IEC mini contactor, 6.60A, 380 Vac, 60 Hz, 2NO-2NO, 6.60A, 45 mm mini, 60 Hz, 0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC mini contactor

UPC

782116884247

Product Height

5 in

Product Weight

1.2 lb

Compliances

RoHS Compliant

CE Marked

Catalog Number

XTMR6A21P

Product Length/Depth

5.25 in

Product Width

5.75 in

Warranty

1 year

Certifications

EN 60947

IEC 60947

UL Listed

CSA Certified

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

6.60A

HP rating - max

0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing mini contactor

Frequency rating

60 Hz

Frame size

45 mm - mini

Terminals

Screw terminals

Coil

380 Vac, 60 Hz

Coil voltage

380 Vac, 50 Hz

Contact configuration

2 NO, 2 NO

Continuous ampere rating

6.60 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTMR 3D Inventor](#)

[XTMR 2D Drawing Xchange](#)

[XTMR AutoCAD 2D Footprint](#)

[XTMR 2D PDF](#)

[XTMR AutoCAD 2D Footprint \(mm\)](#)

[XTMR 3D Model Xchange](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

[Contactors Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - XTMR6A21P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)