

Eaton XTMR6A21TD

Catalog Number: XTMR6A21TD

Eaton XT IEC mini contactor, 6.60A, 24 Vdc, 2NO-2NO, 6.60A, 45 mm mini, 0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor

General specifications

Product Name	Catalog Number
Eaton XT IEC mini contactor	XTMR6A21TD
UPC	Product Length/Depth
782116884285	5.25 in
Product Height	Product Width
5 in	5.75 in
Product Weight	Warranty
1.2 lb	1 year
Compliances	Certifications
CE Marked	IEC 60947
RoHS Compliant	EN 60947
	CSA Certified
	UL Listed

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



defaultTaxonomyAttributeLabel

Amperage Rating

6.60A

HP rating - max

0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH
@115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing mini contactor

Frame size

45 mm - mini

Terminals

Screw terminals

Coil

24 Vdc

Coil voltage

24 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

6.60 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTMR 3D Inventor

XTMR AutoCAD 2D Footprint (mm)

XTMR 2D Drawing Xchange

XTMR AutoCAD 2D Footprint

XTMR 2D PDF

XTMR 3D Model Xchange

Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Contactors Explained

Specifications and datasheets

Eaton Specification Sheet - XTMR6A21TD



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)