

# Eaton XTMR6A21WD

Catalog Number: XTMR6A21WD

Eaton XT IEC mini contactor, 6.60A, 48 Vdc, 2NO-2NO, 6.60A, 45 mm mini, 0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor

## General specifications



Photo is representative

### Product Name

Eaton XT IEC mini contactor

### UPC

782116884315

### Product Height

5 in

### Product Weight

1.2 lb

### Compliances

CE Marked

RoHS Compliant

### Catalog Number

XTMR6A21WD

### Product Length/Depth

5.25 in

### Product Width

5.75 in

### Warranty

1 year

### Certifications

CSA Certified

IEC 60947

UL Listed

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

6.60A

### HP rating - max

0.25, 0.75, 1/ 1.5, 2, 3, 3 hp (1/3PH  
@115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing mini contactor

### Frame size

45 mm - mini

### Terminals

Screw terminals

### Coil

48 Vdc

### Coil voltage

48 Vdc

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

6.60 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTMR AutoCAD 2D Footprint](#)

[XTMR 3D Inventor](#)

[XTMR AutoCAD 2D Footprint \(mm\)](#)

[XTMR 2D PDF](#)

[XTMR 2D Drawing Xchange](#)

[XTMR 3D Model Xchange](#)

### Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTMR6A21WD](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)