

Eaton XTMR9A21B

Catalog Number: XTMR9A21B

Eaton XT IEC mini contactor, 8.80A, 220V 50Hz, 240V 60hz, 2NO-2NO, 8.80A, 45 mm mini, 50-60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

General specifications



Product Name	Catalog Number
Eaton XT IEC mini contactor	XTMR9A21B
UPC	Product Length/Depth
782116884353	5.25 in
Product Height	Product Width
5 in	5.75 in
Product Weight	Warranty
1.2 lb	1 year
Compliances	Certifications
RoHS Compliant	IEC 60947
CE Marked	UL Listed
	CSA Certified
	EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

8.80A

HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing mini contactor

Frequency rating

50-60 Hz

Frame size

45 mm - mini

Terminals

Screw terminals

Coil

220-240 Vac, 50/60 Hz

Coil voltage

220-240 Vac, 50/60 Hz

Contact configuration

2 NO, 2 NO

Continuous ampere rating

8.80 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTMR AutoCAD 2D Footprint \(mm\)](#)

[XTMR 3D Inventor](#)

[XTMR 2D Drawing Xchange](#)

[XTMR 2D PDF](#)

[XTMR AutoCAD 2D Footprint](#)

[XTMR 3D Model Xchange](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

[Contactors Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - XTMR9A21B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)