

# Eaton XTMR9A21E

Catalog Number: XTMR9A21E

Eaton XT IEC mini contactor, 8.80A, 208 Vac, 60 Hz, 2NO-2NO, 8.80A, 45 mm mini, 60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC mini contactor	XTMR9A21E
<b>UPC</b>	<b>Product Length/Depth</b>
782116884391	5.25 in
<b>Product Height</b>	<b>Product Width</b>
5 in	5.75 in
<b>Product Weight</b>	<b>Warranty</b>
1.2 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	IEC 60947
CE Marked	UL Listed
	CSA Certified
	EN 60947

## Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

8.80A

### HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing mini contactor

### Frequency rating

60 Hz

### Frame size

45 mm - mini

### Terminals

Screw terminals

### Coil

208 Vac, 60 Hz

### Coil voltage

208 Vac, 60 Hz

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

8.80 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTMR 3D Model Xchange](#)

[XTMR 2D Drawing Xchange](#)

[XTMR 2D PDF](#)

[XTMR AutoCAD 2D Footprint](#)

[XTMR 3D Inventor](#)

[XTMR AutoCAD 2D Footprint \(mm\)](#)

### Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTMR9A21E](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)