

Eaton XTMR9A21R

Catalog Number: XTMR9A21R

Eaton XT IEC mini contactor, 8.80A, 12 Vac, 50-60 Hz, 2NO-2NO, 8.80A, 45 mm mini, 50-60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor

General specifications



Photo is representative

Product Name

Eaton XT IEC mini contactor

UPC

782116884469

Product Height

5 in

Product Weight

1.2 lb

Compliances

CE Marked

RoHS Compliant

Catalog Number

XTMR9A21R

Product Length/Depth

5.25 in

Product Width

5.75 in

Warranty

1 year

Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

8.80A

HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing mini contactor

Frequency rating

50-60 Hz

Frame size

45 mm - mini

Terminals

Screw terminals

Coil

12 Vac, 50/60 Hz

Coil voltage

12 Vac, 50-60 Hz

Contact configuration

2 NO, 2 NO

Continuous ampere rating

8.80 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTMR 3D Inventor

XTMR AutoCAD 2D Footprint (mm)

XTMR 3D Model Xchange

XTMR 2D PDF

XTMR 2D Drawing Xchange

XTMR AutoCAD 2D Footprint

Multimedia

Contactors Explained

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Specifications and datasheets

Eaton Specification Sheet - XTMR9A21R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)