

# Eaton XTMR9A21W

Catalog Number: XTMR9A21W

Eaton XT IEC mini contactor, 8.80A, 42 Vac, 50 Hz, 48 Vac, 60 Hz, 2NO-2NO, 8.80A, 45 mm mini, 50-60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



Photo is representative

### Product Name

Eaton XT IEC mini contactor

### UPC

782116884513

### Product Height

5 in

### Product Weight

1.2 lb

### Compliances

CE Marked

RoHS Compliant

### Catalog Number

XTMR9A21W

### Product Length/Depth

5.25 in

### Product Width

5.75 in

### Warranty

1 year

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

8.80A

### HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing mini contactor

### Frequency rating

50-60 Hz

### Frame size

45 mm - mini

### Terminals

Screw terminals

### Coil

42 Vac, 50/60 Hz

### Coil voltage

42-48 Vac, 50/60 Hz

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

8.80 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

XTMR 2D Drawing Xchange

XTMR 2D PDF

XTMR 3D Model Xchange

XTMR AutoCAD 2D Footprint (mm)

XTMR 3D Inventor

XTMR AutoCAD 2D Footprint

### Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Contactors Explained

### Specifications and datasheets

Eaton Specification Sheet - XTMR9A21W



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)