

# Eaton XTPT20BC1NL

Catalog Number: XTPT20BC1NL

Eaton XT IEC FVR Manual Motor Controller, 0.63A, 45 mm Frame size, 48V 50 Hz coil

## General specifications



Photo is representative

### Product Name

Eaton XT IEC motor control

### Catalog Number

XTPT20BC1NL

### EAN

4015080889182

### Product Length/Depth

1.77 in

### Product Height

3 in

### Product Width

3.66 in

### Product Weight

0.65 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked  
DIN VDE 0600

### Certifications

UL Listed  
CSA file No. 229767, Class 3211-05  
UL Listed file E245398  
UL 508  
CSA Certified  
IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

20A

### Overload range

16-20 A

### Type

High magnetic

### Frame size

45 mm

### Frame

B

### Trip type

Class 10

## Resources

### Catalogs

[Motor Control and Protection](#)

### Specifications and datasheets

[Global Data Sheet - XTPT20BC1NL](#)

[Eaton Specification Sheet - XTPT20BC1NL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)