

Eaton XTSC001BBMT

Catalog Number: XTSC001BBMT

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 14A, Factory-assembled, B-frame, 24V/50 or 60 Hz coil, 1NO-1NC, Three-phase, 1A

General specifications



Photo is representative

Product Name

Eaton XT IEC motor control

UPC

786680186707

Product Height

7.03 in

Product Weight

4 lb

Catalog Number

XTSC001BBMT

Product Length/Depth

1.77 in

Product Width

3.77 in

Certifications

UL Listed

CSA Certified

Catalog Notes

For 200 and 240V horsepower rating calculate motor rating according to rated current. Specified values to NEC 430.6(A)(1).

Amperage Rating

1A

HP rating - max

1/2 Hp at 480 and 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

24 Vac, 50/60 Hz

Frame

B

Full load current range

0.63-1 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 14A

Phase

Three-phase

Class

Class 10

Trip type

Class 10

Catalogs[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSC001BBMT](#)