

Eaton XTSC004BBMA-AE

Catalog Number: XTSC004BBMA-AE

Eaton XT IEC FVNR Manual Combination Motor Controller, Factory assembled, B-frame 45mm MMP, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 56A, 110V/50 Hz, 120V/60 Hz coil, 1NO-1NC, Three-phase, 4A, 110V/50 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton XT IEC motor control	XTSC004BBMA-AE
UPC	Product Length/Depth
786689060886	1.77 in
Product Height	Product Width
7.03 in	3.77 in
Product Weight	Certifications
4 lb	IEC 60947-4-1
	UL 508
	CE
	UL Listed file E245398

Catalog Notes

Includes XTPAXLSA MMP Line Side Adapter

defaultTaxonomyAttributeLabel

Amperage Rating

4A

Overload range

2.5-4 A

Frame size

45 mm, 0.1 to 32 A MMP, 45 mm, 7 to 15 A contactor

Auxiliary contacts

1 NO, 1 NC

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact rating

4 A

Frame

B MMP + B Contactor

Full load current range

2.5-4 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 56A

Phase

Three-phase

Class

Class 10

Resources

Catalogs

[Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTSC004BBMA-AE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)