

Eaton XTSC010BBMH

Catalog Number: XTSC010BBMH

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 140A, Factory-assembled, B-frame, 240V/50 Hz, 277V/60 Hz coil, 1NO-1NC, Three-phase, 10A

Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC motor control	XTSC010BBMH
UPC	Product Length/Depth
786680186097	1.77 in
Product Height	Product Width
7.03 in	3.77 in
Product Weight	Certifications
4 lb	UL Listed
	CSA Certified



defaultTaxonomyAttributeLabel

Amperage Rating

10A

HP rating - max

3 Hp at 200 and 240V, 7-1/2 Hp at 480V, 7.5 Hp at 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

240-277 Vac, 50/60 Hz

Frame

B

Full load current range

6.3-10 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 140A

Phase

Three-phase

Class

Class 10

Trip type

Class 10

Resources

Catalogs

[Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTSC010BBMH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)