

Eaton XTSC012BBMF

Catalog Number: XTSC012BBMF

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 168A, Factory-assembled, B-frame, 230V/50 Hz coil, 1NO-1NC, Three-phase, 12A

General specifications



Product Name

Eaton XT IEC motor control

Catalog Number

XTSC012BBMF

UPC

786680186523

Product Length/Depth

1.77 in

Product Height

7.03 in

Product Width

3.77 in

Product Weight

4 lb

Certifications

UL Listed

CSA Certified

Photo is representative

Amperage Rating

12A

HP rating - max

3 Hp at 200 and 240V, 7-1/2 Hp at 480V, 7.5 Hp at 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

230 Vac, 50 Hz

Frame

B

Full load current range

8-12 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 168A

Phase

Three-phase

Class

Class 10

Trip type

Class 10

Catalogs[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSC012BBMF](#)