

# Eaton XTSC012BBML

Catalog Number: XTSC012BBML

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 168A, Factory-assembled, B-frame, 380V/50 Hz, 440V/60 Hz coil, 1NO-1NC, Three-phase, 12A

## General specifications



### Product Name

Eaton XT IEC motor control

### UPC

786680186547

### Product Height

7.03 in

### Product Weight

4 lb

### Catalog Number

XTSC012BBML

### Product Length/Depth

1.77 in

### Product Width

3.77 in

### Certifications

UL Listed

CSA Certified

Photo is representative

## defaultTaxonomyAttributeLabel

### Amperage Rating

12A

### HP rating - max

3 Hp at 200 and 240V, 7-1/2 Hp at 480V, 7.5 Hp at 600V

### Type

Factory-assembled

### Frame size

45 mm, 0.1 to 32 A

### Auxiliary contacts

1 NO, 1 NC

### Coil voltage

380-440 Vac, 50/60 Hz

### Frame

B

### Full load current range

8-12 A

### Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 168A

### Phase

Three-phase

### Class

Class 10

### Trip type

Class 10

## Resources

### Catalogs

[Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTSC012BBML](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)