

Eaton XTSC016BBMA

Catalog Number: XTSC016BBMA

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A, Factory-assembled, B-frame, 110V/50 Hz, 120V/60 Hz coil, 1NO-1NC, Three-phase, 16A

General specifications



Product Name

Eaton XT IEC motor control

Catalog Number

XTSC016BBMA

UPC

786680186943

Product Length/Depth

1.77 in

Product Height

7.03 in

Product Width

3.77 in

Product Weight

4 lb

Certifications

UL Listed

CSA Certified

Photo is representative

defaultTaxonomyAttributeLabel

Amperage Rating

16A

HP rating - max

3 Hp at 200 and 240V, 10 Hp at 480V, 7.5 Hp at 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

110-120 Vac, 50/60 Hz

Frame

B

Full load current range

10-16 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A

Phase

Three-phase

Class

Class 10

Trip type

Class 10

Resources

Catalogs

[Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTSC016BBMA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)