

Eaton XTSC016BBMT

Catalog Number: XTSC016BBMT

Eaton IEC motor control , Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A, Factory-assembled, B-frame, 24V/50 or 60 Hz coil, 1NO-1NC, Three-phase, 16A

General specifications



Product Name

Eaton XT IEC motor control

Catalog Number

XTSC016BBMT

UPC

786680186578

Product Length/Depth

1.77 in

Product Height

7.03 in

Product Width

3.77 in

Product Weight

4 lb

Certifications

UL Listed

CSA Certified

Photo is representative



Powering Business Worldwide

Amperage Rating

16A

HP rating - max

3 Hp at 200 and 240V, 10 Hp at 480V, 7.5 Hp at 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

24 Vac, 50/60 Hz

Frame

B

Full load current range

10-16 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A

Phase

Three-phase

Class

Class 10

Trip type

Class 10

Catalogs

[Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - XTSC016BBMT](#)