

# Eaton XTSC2P5BBMA-AE

Catalog Number: XTSC2P5BBMA-AE

Eaton XT IEC FVNR Manual Combination Motor Controller, Factory assembled, B-frame 45mm MMP, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 35A, 110V/50 Hz, 120V/60 Hz coil, 1NO-1NC, Three-phase, 2.5A,110V/50

## General specifications



Photo is representative

### Product Name

Eaton XT IEC motor control

### UPC

786689060862

### Product Height

7.03 in

### Product Weight

4 lb

### Catalog Number

XTSC2P5BBMA-AE

### Product Length/Depth

1.77 in

### Product Width

3.77 in

### Certifications

IEC 60947-4-1

CE

UL Listed file E245398

UL 508

### Catalog Notes

Includes XTPAXLSA, MMP Line Side

Adapter

## defaultTaxonomyAttributeLabel

### Amperage Rating

2.5A

### Overload range

1.6-2.5 A

### Frame size

45 mm, 0.1 to 32 A MMP, 45 mm, 7 to 15 A contactor

### Auxiliary contacts

1 NO, 1 NC

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact rating

2.5 A

### Frame

B MMP + B Contactor

### Full load current range

1.6-2.5 A

### Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 35A

### Phase

Three-phase

### Class

Class 10

## Resources

### Catalogs

[Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTSC2P5BBMA-AE](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)