

# Eaton XTSC6P3BBMH

Catalog Number: XTSC6P3BBMH

Eaton XT IEC FVR Manual Motor Controller, 6.3A, 45 mm Frame size, 220 Vdc coil

## General specifications



**Product Name**  
Eaton XT IEC motor control

**Catalog Number**  
XTSC6P3BBMH

**UPC**  
786680187063

**Product Length/Depth**  
1.77 in

**Product Height**  
7.03 in

**Product Width**  
3.77 in

**Product Weight**  
4 lb

**Certifications**  
UL Listed file E245398  
IEC 60947  
UL 508

Photo is representative

**Amperage Rating**

6.30A

**HP rating - max**

1-1/2 Hp at 200 and 240V, 3 Hp at 480V, 5 Hp at 600V

**Type**

Factory-assembled

**Frame size**

45 mm, 0.1 to 32 A

**Auxiliary contacts**

1 NO, 1 NC

**Coil voltage**

240-277 Vac, 50/60 Hz

**Frame**

B

**Full load current range**

4-6.3 A

**Special features**

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 88.2A

**Phase**

Three-phase

**Class**

Class 10

**Catalogs**[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSC6P3BBMH](#)